











### A revolution in appearance measurement



#### Optimap2 PSB

## Complete surface analysis

Optimap2, the unique portable solution for surface inspection allows rapid large area measurement and analysis of all types of coated or uncoated surfaces. Powerful on-screen functionality includes cross-sectional viewing allowing detection and characterisation of common surface irregularities including defects and waviness. In quality control, inferior surface evaluation methods are still commonplace.

Many methods are subjective, time consuming and lack definition. Modern consumers demand high quality products with surface finishes that are homogenous and free from defects

The Optimap2 provides a unique solution to these measurement challenges providing quantifiable data for improved production control

#### Sample applications for the Optimap2 PSD



Paints & coatings



manufacturers







**Metal Polishers** 



Polished Stone



Smart phone, tablet PC and laptop covers



Automotive re-finish



Wood coatings



### Reflected image quality measurement



## RHOPOINT

## Multi-angle gloss, haze, distinctness of image meter

Using patented technology, the Rhopoint IQ provides a unique solution for the measurement of haze and orange peel. Although visible to the naked eye, they are not detected by a standard glossmeter.

By measuring the quality of the reflected image it is the only hand held instrument that truly profiles how light is reflected from a surface.

In one guick and easy operation the IQ not only measures gloss at three angles but also measures haze, DOI (distinctness of image) and RSPEC (specular reflectance) providing a detailed analysis of the image forming quality of the surface.

#### Sample applications for the Rhopoint IQ



Paints & coatings

Wood coatings



Yacht manufacturers





Automotive



**Metal Polishers** 



Polished Stone



Smart phone, tablet PC and laptop covers



Printing ink



Automotive re-finish

### Characterise surface quality of small areas



## RHOPOINT (

# 20° gloss, haze & distinctness of image meter

The Rhopoint IQ FLEX 20 brings gloss, haze and distinctness of image measurement to a new format. It is specifically designed for small areas and curved surfaces that cannot be accurately measured with traditional glossmeters.

The Rhopoint IQ FLEX 20 can be customised with magnetically attached adaptor plates. These can be easily interchanged for

different applications and provide reduced measurement areas as low as 2mm.

To increase the repeatability of curved surface measurement, alternative adaptor plates can be designed for specific samples.

#### Sample applications for the Rhopoint IQ Flex 20



Yacht manufacturers



Plastics Industry



Curved surfaces



Tablet PC



Automotive Interior



Automotive



Mobile phones

#### Low gloss measurement





# 60° glossmeter for low gloss surfaces

Designed specifically to measure the gloss of surfaces that cannot be measured using traditional glossmeters, the Novo-Gloss Flex 60 Glossmeter combines the functionality and reporting of an advanced glossmeter withan ultra lightweight remote measuring head.

The Novo-Gloss Flex 60 has been designed specifically to measure low gloss surfaces. It

features an additional measuring scale with a resolution 10 times greater than standard glossmeters. This increased resolution gives a far superior level of control of surface finish.

The Novo-Gloss Flex 60 complies to ISO 2813 and ASTM D523. Measurements are made with the instrument are compatible with traditional glossmeters complying to these standards.

#### Sample applications for the Novo-Gloss Flex 60



Curved plastic parts



Automotive



Mobile phones



Automotive interior



Plastics industry

#### **Transmission Hazemeter**



# NOVO-HAZE

# Measure total transmission and haze

The instrument features an intuitive user friendly interface which minimises the test time and makes it an ideal choice for both QC and R&D.

Uncompromising design, high quality materials make the Novo-Haze TX the ideal choice for any laboratory or QA environment. At 50% of the price of the market leader for ASTM D1003 (CIE C) measuring instrument, the Rhopoint Novo-Haze TX represents huge savings without compromising measurement accuracy.







Viewed through material with low haze

Viewed through material with higher haze

#### Accuracy in all gloss applications



# NOVO-GLOSS\*\*\*\*

## Single, dual and trigloss glossmeters

Single, dual and trigloss glossmeters are high specification hand held instruments for measuring gloss.

Gloss is an aspect of the visual perception of objects that is as important as colour when considering the psychological impact of products on a consumer. Maintaining consistent gloss levels on every product or across different batches of a product is vital

for manufacturers seeking maximum appeal of their finished goods.

The advanced features of the instrument include user definable batches for more efficient measurement of multiple samples, direct data input via bluetooth into Microsoft Excel and pass/fail for easy identification of non-conformances

#### Sample applications for the Novo-Gloss range



Paints & coatings



Yacht manufacturers



**Metal Polishers** 



Polished stone



Powder coating



**Furniture** 



Smart phone, tablet PC and laptop covers



Wood coatings



Automotive



Printing ink



Plastics industry



Automotive re-finish



Automotive coatings

#### Shade & opacity measurement



## RHOPOINT NOVO-SHADE DUO+

# Measure shade, opacity and cleanliness

The Novo-Shade Duo+ is a versatile solution for reflectometry measurement. Its standard configured geometry of 45°/0° allows objective measurements of the shade or opacity of a surface. In shade mode, applications include the measurement of colour fading in textiles and plastics, shade of paints, inks and coatings, chalking of paint, efficiency of detergents and bleaching agents, whiteness of recycled paper and the

cleanliness and oxidisation of metal surfaces. Whilst in opacity mode, applications include the measurement of the hiding power of paints, inks and coatings, transparency of plastic films and opacity of paper.

Its in-built automatic calibration ensures accurate measurements are guaranteed every time the instrument is used.

#### Sample applications for the Novo-Shade Duo+, opacity and shade



Hiding power of paints, inks and coatings



Transparency of plastic film



Opacity of paper



Shade of paints, inks and coatings



Fading of textiles and plastics



Chalking of paint



Efficiency of detergents and bleaching agents



Whiteness of recycled paper



Cleanliness and oxidisation on metal surfaces

#### Curved surface gloss measurement



#### NOVO-CURVE™

## 60° bench glossmeter

The Novo-Curve™ is a unique bench top instrument designed for the gloss measurement of curved surfaces and small areas that are difficult to measure with standard glossmeters. The large sample platform allows hands free measurement by simply placing the item over the measuring aperture.

Four adjustable jigging posts are also available to provide consistency in sample positioning. Statistical data is stored internally in the instrument memory and can be either viewed on screen or by downloading to PC using the Novo-Soft software supplied.

#### Sample applications for the Novo-Curve™



**Automotive** 



**Furniture** 



Ceramics



Medical and confectionery



Coins



**Banknotes** 



**Dental Research** 



Electroplating

### Test equipment for the packaging industry





# Plastics, films paper and board

Rhopoint Instruments manufacture the Hanatek branded test equipment for the flexible packaging industry. The products in the range are designed to increase packaging speeds and reduce raw material wastage.

All products conform to relevant ISO and ASTM standards and are manufactured in the UK in an ISO 9001 environment.

Instruments in the range include:

**Friction Testers**: Designed for testing static and dynamic coefficient of friction.

**Rub & Abrasion Tester**: Tests the rub resistance of inks and coatings.

**Carton Crease Testers**: Measure board stiffness, crease recovery, whole carton opening force and create custom crease profiles.

Thickness Gauges: Measure down to  $0.01\mu m$  resolution with fixed pressure to ASTM and ISO standards.

#### Hantek Instruments



Precision Thickness Tester



Carton Crease Proofer



Crease & Board Stiffness Tester



Carton Force Analyser



Advanced Friction Tester



Compact Friction Tester



Rub Resistance Tester



Melt Flow Indexer



Film Shrink Tester

## Instruments for testing paints & liquid coatings



## PAINTLAB+ 0

# Liquid coating test instruments

Rhopoint Instruments manufacture the Paintlab+ branded test equipment for liquid coatings.

The viscosity product range starts with flow cups which conform to a variety ofstandards and also includes viscometers: Krebs, Cone & Plate and Viscomixer which are all supplied with integrated temperature monitoring

Calibration oils are available with UKAS / ISO 17025 certification.

The Rhopoint Minimum Film Forming Temperature (MFFT) can be found in the laboratories of many of world's leading coatings producers.

The Pfund cryptometer provides a quick measure of opacity of liquid coatings.

#### Paintlab+ Instruments



Minimum Film Forming Temperture Bar



Krebs Viscometer



Cone & Plate Viscometer



Viscomixer



Cryptometer





Flow Cups

Calibration Oils











**Rhopoint Instruments Ltd.** is a member of the **Rhopoint Group** 



Rhopoint Instruments Limited • Rhopoint House • Enviro 21 Park • Queensway Ave. South • St Leonards on Sea • East Sussex • TN38 9AG • Tel: +44 (0)1424 739622 sales@rhopointinstruments.com • www.rhopointinstruments.com