

ATI

ADVANCED TESTING INSTRUMENTS



FIBER TESTING
INSTRUMENTS
**TB510B SAW GIN
FLOOR-TYPE**

TB510B SAW GIN FLOOR-TYPE

Saw Gin Floor-type is used for separating seed cotton. After ginning, cotton fiber with trash, leaf, dust, etc. is collected, and cottonseed with a little clean lint is collected in another container.

This lab model gin is conveniently used for trial ginning and as the pre-process of cotton trash analyzer at cotton collecting point and plant, laboratory, etc.

SPECIFICATIONS

- High efficiency cleaning unit and feeding roller, running is stable and reliable
- Simple driving system, low impact, low noise
- Safe operation and power saving
- Can be placed on study ground at work
- Work capacity 300 kg/h
- Saw 20pcs

STANDARDS: JB-T 7884.1

POWER: 220 V / 380 V 50 Hz 2.2 kW / 4 kW

WEIGHT: 300 kg

DIMENSIONS: 1400 x 800 x 1300 mm (L x W x H)

